



Product Quick Search

[HOME](#) | [WHERE TO BUY](#) | [CONTACT US](#) | [SITE MAP](#)

- PRODUCTS
- SUPPORT
- NEWS/EVENTS
- ABOUT BALDOR
- INVESTOR RELATIONS

General Information

- [Overview](#)
- [Specifications](#)**
- [Performance Data](#)
- [Parts List](#)
- [Dimensional Dwg](#)
- [Connection Diag](#)
- [Product Literature](#)
- [More Information](#)**
- [Locate Distributor](#)
- [Baldor Sales Offices](#)

[Return to List](#)

[AC Motors](#) | [Washdown](#) |

Specifications: CWDL3504

Catalog Number:	CWDL3504
Specification Number:	35S576-0154G1
Horsepower:	.5
Voltage:	115/230
Hertz:	60
Phase:	1
Full Load Amps:	8/4
Usable at 208 Volts:	4.7
RPM:	1725
Frame Size:	56C
Service Factor:	1.25
Rating:	40C AMB-CONT
Locked Rotor Code:	L
NEMA Design Code:	N
Insulation Class:	F
Full Load Efficiency:	64
Power Factor:	63
Enclosure:	TEFC
Baldor Type:	3520L
DE Bearing:	6205
ODE Bearing:	6203
Electrical Specification Number:	35WG0154
Mechanical Specification Number:	35S576
Base:	RG
Mounting:	F1

* For certified information, contact your local [Baldor office](#).

[Products](#) | [Support](#) | [News/Events](#) | [About Baldor](#) | [Investor Relations](#) | [Home](#)

Baldor Electric Company is an equal opportunity employer.
Copyright © 2001-2007 Baldor Electric Company. All rights reserved.
This site works best with Internet Explorer and Netscape 4.x and above.