



Product Quick Search



[HOME](#) | [WHERE TO BUY](#) | [CONTACT US](#) | [SITE MAP](#)

PRODUCTS

SUPPORT

NEWS/EVENTS

ABOUT BALDOR

INVESTOR RELATIONS

**General Information**

- [Overview](#)
- [Specifications](#)
- [Performance Data](#)
- [Parts List](#)
- [Dimensional Dwg](#)
- [Connection Diag](#)
- [Product Literature](#)
- [More Information](#)
- [Locate Distributor](#)
- [Baldor Sales Offices](#)

◀ [Return to List](#)

[AC Motors](#) | [General Purpose](#) |

## Specifications: L3507

Catalog Number:	L3507
Specification Number:	34G426Y094
Horsepower:	.75
Voltage:	115/230
Hertz:	60
Phase:	1
Full Load Amps:	8.4/4.2
Usable at 208 Volts:	5.4
RPM:	1725
Frame Size:	56
Service Factor:	1.25
Rating:	40C AMB-CONT
Locked Rotor Code:	J
NEMA Design Code:	N
Insulation Class:	B
Full Load Efficiency:	72
Power Factor:	78
Enclosure:	TEFC
Baldor Type:	3428LC
DE Bearing:	6203
ODE Bearing:	6203
Electrical Specification Number:	34WGY094
Mechanical Specification Number:	34G426
Base:	RG
Mounting:	F1

\* For certified information, contact your local [Baldor office](#).

[Products](#) | [Support](#) | [News/Events](#) | [About Baldor](#) | [Investor Relations](#) | [Home](#)