

- Sheet Metal Screws
- Pan Head
- Phillips
- Stainless Steel

Stainless steel pan head phillips sheet metal screws will tap their own mating threads when driven into preformed holes in metal. Length is determined from the base of the fastener. Stainless steel resists corrosion and is ideal for applications where chemical resistance is required.



CAT NO	UPC		SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
PHSMSS8114	70226	#8	8 x 1-1/4	100	500	5000	0.61#	C
PHSMSS8112	70228		8 x 1-1/2	100	500	5000	0.69#	C
PHSMSS82	70230		8 x 2	100	500	5000	0.89#	C
PHSMSS1012	70240	#10	10 x 1/2	100	500	5000	0.43#	C
PHSMSS1034	70242		10 x 3/4	100	500	5000	0.54#	C
PHSMSS101	70244		10 x 1	100	500	5000	0.69#	C
PHSMSS10114	70246		10 x 1-1/4	100	500	5000	0.80#	C
PHSMSS10112	70248		10 x 1-1/2	100	500	5000	0.91#	C
PHSMSS102	70250		10 x 2	100	500	5000	1.17#	C

Slotted Hex Washer Head Sheet Metal Screws • Zinc Plated | PC 4000

- Sheet Metal Screws
- Hex Washer Head
- Slotted
- Zinc Plated Steel

Hex washer head sheet metal screws will tap their own mating threads when driven into preformed holes in metal. Length is determined from the base of the fastener.



CAT NO	UPC		SIZE	HEX SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT	
HWSMS612	56500	#6	6 x 1/2	1/4"	100	500	5000	0.25#	C	
HWSMS634	56502		6 x 3/4	1/4"	100	500	5000	0.30#	C	
HWSMS61	56504		6 x 1	1/4"	100	500	5000	0.38#	C	
HWSMS6114	56506		6 x 1-1/4	1/4"	100	500	5000	0.45#	C	
HWSMS6112	56508		6 x 1-1/2	1/4"	100	500	5000	0.52#	C	
HWSMS62	56510		6 x 2	1/4"	100	500	5000	0.62#	C	
HWSMS812	56550	#8	8 x 1/2	1/4"	100	500	5000	0.33#	C	
HWSMS834	56552		8 x 3/4	1/4"	100	500	5000	0.43#	C	
HWSMS81	56554		8 x 1	1/4"	100	500	5000	0.53#	C	
HWSMS8114	56556		8 x 1-1/4	1/4"	100	500	5000	0.69#	C	
HWSMS8112	56558		8 x 1-1/2	1/4"	100	500	3000	0.73#	C	
HWSMS82	56560		8 x 2	1/4"	100	500	3000	0.92#	C	
HWSMS8212	56562		8 x 2-1/2	1/4"	100		3000	0.33#	C	
HWSMS83	56564		8 x 3	1/4"	100		3000	1.34#	C	
HWSMS1012	56600	#10	10 x 1/2	5/16"	100	500	5000	0.46#	C	
HWSMS1034	56602		10 x 3/4	5/16"	100	500	5000	0.57#	C	
HWSMS101	56604		10 x 1	5/16"	100	500	5000	0.73#	C	
HWSMS10114	56606		10 x 1-1/4	5/16"	100	500	3000	0.84#	C	
HWSMS10112	56608		10 x 1-1/2	5/16"	100	500	3000	0.96#	C	
HWSMS102	56610		10 x 2	5/16"	100	500	3000	1.22#	C	
HWSMS10212	56612		10 x 2-1/2	5/16"	100		3000	1.44#	C	
HWSMS103	56614		10 x 3	5/16"	100		3000	1.81#	C	
HWSMS1234	56650		#12	12 x 3/4	5/16"	100	500	5000	0.85#	C
HWSMS121	56652			12 x 1	5/16"	100	500	5000	0.98#	C
HWSMS12114	56654	12 x 1-1/4		5/16"	100	500	3000	1.14#	C	
HWSMS12112	56656	12 x 1-1/2		5/16"	100	500	3000	1.31#	C	
HWSMS122	56658	12 x 2		5/16"	100		3000	1.61#	C	
HWSMS12212	56660	12 x 2-1/2		5/16"	100		3000	1.98#	C	
HWSMS123	56662	12 x 3		5/16"	100		3000	2.33#	C	
HWSMST834	17267	#8		<b>Tuff Pack</b>	8 x 3/4	1/4"	500	3000	2.21#	C
HWSMST81	17268		8 x 1		1/4"	500	3000	2.71#	C	
HWSMST1034	17269	#10		10 x 3/4	5/16"	500	3000	3.10#	C	
HWSMST101	17270			10 x 1	5/16"	500	3000	3.59#	C	

See new products at [www.lhdottie.com](http://www.lhdottie.com)

UPC Vendor ID Code: 78-1002

