



**Item ID:** 61-701

**Name:** 200 Amp Clamp Meter

**Downloads:** [Instruction Sheet](#)

**Calibration Procedure:** [Calibration Procedure](#)

- Features:**
- Non-contact voltage
  - Capacitance
  - 200A Current capability
  - Audible continuity
  - Diode Test
  - Data hold/max hold
  - Low battery indicator
  - Overload protection on all ranges
  - Silicone leads
  - Cat III - 600V rated
  - Audible dangerous voltage warning
  - Sleep mode
  - Ergonomic hourglass shape
  - Compact head design
  - Includes carrying case
  - Lifetime limited warranty

61-701 Specifications	Range & Resolution	Basic Accuracy
AC Voltage	200.0/600V	1.2%
DC Voltage	20.00/200.0/600V	0.5%
AC Current	200.0A	3.0%
Resistance	200.0/200.0k $\Omega$	1.0%
Capacitance	200.0 $\mu$ F	3.0%
Frequency	2.000k/20.00k/40.00k Hz	0.1%