



Sta-Kon®

T&B Catalog Number:

10RC-10FL

UPC Number:

78621080726

Description:

Insulated Vinyl Locking Fork Terminal For Wire Range 12-10 Stud Size #10, Yellow

Status:

Active

Features

Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.

General

Insulation Type	Insulated Vinyl
Terminal Series	RC
Material	Copper
Finish	Electro -Tin Plated
Color	Yellow
Wire Range	12-10
Stud Size	#10

Specifications

Temperature Rating	105°C
Flammability Rating	UL 94 V-0

Dimension Information

A (inches)	1.09
B (inches)	.37
C (inches)	.27
M (inches)	.90
Maximum Insulation (inches)	.220
Stock Thickness	.04

Packaging

Package Quantity	50
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.54 lbs. per 100
Package Qty	50
Alternate Package Qty	RC2227

Tooling

Application Tools	ERG2001, ERG2003, WT145C, WT2000, WT112M, WT145C
-------------------	--

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com