



Sta-Kon®

T&B Catalog Number: 2RB14X
UPC Number: 78621080720
Description: Expanded Insulated Vinyl Butt Splice Connector For Wire Range 16-14 Length 1.13 Diameter .26, Blue
Status: Active

Features

In butt splices, the wires are butted together and crimped at each end of the splice. These splices are color-coded according to wire size.

General

Insulation Type	Expanded Insulated Vinyl
Terminal Series	RB
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14

Specifications

Temperature Rating	105°C
Flammability Rating	UL 94 V-0

Dimension Information

A (inches)	1.13
B (inches)	.26
Maximum Insulation (inches)	.155
Stock Thickness	.03

Packaging

Package Quantity	100
Package in Units	5000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.42 lbs. per 100
Alternate Package Qty	RBB217200

Tooling

Application Tools	WT145C, WT2000, WT112M, ERG2001, ERG2003
-------------------	--

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com