



Catamount®

T&B Catalog Number**UPC Number:****Description:****L-8-40-0-C:**

72849491820

Cable Tie 40lb 8" Ultraviolet Resistant
Black All-Nylon 100 Per Bag**Status:**

Active

General

Material	Nylon 6.6 Weather Resistant
Color	Black

Specifications

Tensile Strength (lbs.)	40
Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Dimension Information

Length (inches)	8.5
Width (inches)	0.130
Max. Wire Bundle Diameter (inches)	2
Min. Wire Bundle Diameter (inches)	1/16

Packaging

Package in Units	10000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2.38 lbs. per 1000

Tooling

Application Tools	QC-100, L-200, L-400-C, ERG-299
-------------------	---------------------------------

Application Support

Overview	Available on Website
T&B Sales Drawings	wsd-000221
Material Selection Guide	Available on Website
Available Colors	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com