



Open Switches

T&B Catalog Number:

UPC Number:
Status:
Description:

OT30FT3
80432541552
Active

3 pole, 30 amps rated at 600 VAC, UL 98, door mounted open non-fusible disconnect switch

Features

Quick make, quick brake mechanism

Extremely compact size

Finger-proof construction with no hazardous exposed parts

Application

Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.

Motor feeder applications and motor feeder short circuit and ground fault protection

General

Style	Door Mounted
Number of Poles	3
Series	Non-fusible

Approvals

UL Class	UL 98
----------	-------

Dimension Information

H x W x D (inches)	3.94 x 2.76 x .88
--------------------	-------------------

Specifications

Rated Current (Amps)	30
Rated Voltage AC	600

Packaging

T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	0.97 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com



Open Switches T&B Catalog Number:

UPC Number: OT30FT3
Status: 80432541552
Description: Active

3 pole, 30 amps rated at 600 VAC, UL 98, door mounted open non-fusible disconnect switch

Features

- Quick make, quick brake mechanism
- Extremely compact size
- Finger-proof construction with no hazardous exposed parts

Application

- Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.
- Motor feeder applications and motor feeder short circuit and ground fault protection

General

Style	Door Mounted
Number of Poles	3
Series	Non-fusible

Approvals

UL Class	UL 98
----------	-------

Dimension Information

H x W x D (inches)	3.94 x 2.76 x .88
--------------------	-------------------

Specifications

Rated Current (Amps)	30
Rated Voltage AC	600

Packaging

T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	0.97 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com