



## Open Switches T&B Catalog Number:

**UPC Number:** OT40FT3  
**Status:** 80432541557  
**Description:** Active

3 pole, 40 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

### Features

Quick make, quick brake mechanism  
 Extremely compact size  
 Finger-proof construction with no hazardous exposed parts

### Application

Industrial control panel disconnects  
 For use in motor controller and motor overload protection applications  
 Can be used as an OSHA lockout/tagout disconnect

### General

Style: Door Mounted  
 Number of Poles: 3  
 Series: Non-fusible

### Approvals

UL Class: UL 508

### Dimension Information

H x W x D (inches): 2.13 x 1.69 x 2.64

### Specifications

Rated Current (Amps): 40  
 Rated Voltage AC: 600

### Packaging

T&B Inner Pack: 1  
 Package in Units: 10  
 T&B Sold in UOM: Each  
 T&B Weight Per UOM: 0.23 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com