



Open Switches T&B Catalog Number:

OT63FT3
80432541561
Active

UPC Number:
Status:
Description:

3 pole, 60 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

Features

Quick make, quick brake mechanism
Extremely compact size
Finger-proof construction with no hazardous exposed parts

Application

Industrial control panel disconnects
For use in motor controller and motor overload protection applications
Can be used as an OSHA lockout/tagout disconnect

General

Style Door Mounted
Number of Poles 3
Series Non-fusible

Approvals

UL Class UL 508

Dimension Information

H x W x D (inches) 2.85 x 2.07 x 2.72

Specifications

Rated Current (Amps) 60
Rated Voltage AC 600

Packaging

T&B Inner Pack 1
Package in Units 10
T&B Sold in UOM Each
T&B Weight Per UOM 0.61 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com