



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



OTM10 250V 10A 1 1/2X13/32 Mid Fuse

Mersen Fuses

Catalog Number	OTM10
Manufacturer	Mersen Fuses
Description	Fuse Otm - Midget - Fast-Acting 250VAC 10A Ferrule Amp-Trap®
Weight per unit	0.0120 (lbs/each)
Product Category	Small Dimension Fuses

Features

AC Voltage Rating	250
amperage rating	10
class	Midget
connection	Ferrule
interrupt rating	10
Voltage Rating	250

Material, Color, and Finish

Body Material	Paper
---------------	-------

Dimensions and Weight

Size	1.5 x 0.41
------	------------

Descriptions

Description	250V 10A 1 1/2X13/32 MID FUSE
extra long description	Mersen OTM10 Fuse OTM - Midget - Fa
Features	One-Time OTM midget fuses provide low-cost protection for 250VAC general purpose lighting, heating, control circuits, etc. where time-delay is not required. (Not for Branch Circuit Protection).
Long Description	Fuse OTM - Midget - Fast-Acting 250VAC 10A Ferrule Amp-Trap®
Product Type	Fuse Otm - Midget - Fast-Acting 250VAC 10A Ferrule
Short Description	250V 10A 1 1/2x13/32 MID FUSE
Special Features	Low cost and fully rated for economy without compromise Can be used with UltraSafe™ fuse holders 1 1/2" x 13/32" (10 mm x 38 mm) dimensions

Manufacturer Information

Brand	Mersen
GTIN	00782001705107
Manufacturers Part Number	OTM10
UPC	782001705107

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	Midget Fuses



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.012

Uses, Certifications, and Standards

Application	Supplemental protection of circuits up to 250VAC and 10kA
Mounting	Clip
standard	UL Listed to standard 248-14, File E33925 CSA Certified to Standard C22.2 No. 248.14