



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton meter socket

1010468CH

UPC:786685703381

### Dimensions:

- **Height:** 29 IN
- **Length:** 5.69 IN
- **Width:** 15 IN

**Weight:**35 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Commercial
- **Amperage Rating:** 320A
- **Feed Type:** Top/bottom
- **Line:** #4-600 kcmil
- **Number Of Jaws:** Four-jaw
- **Phase:** Single-phase
- **Accessories:** Anti-inversion clips
- **Bypass:** Lever
- **Number Of Sockets:** 1
- **Voltage Rating:** 600V

### Supporting documents:

- [Dimensional Drawing - AE #E-1045 SKT 320A 1P HCP](#)
- [Eaton Specification Sheet - 1010468CH](#)

### Certifications:

- UL Listed

**Product compliance:** No Data







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton meter socket

1010468CH

UPC:786685703381

### Dimensions:

- **Height:** 29 IN
- **Length:** 5.69 IN
- **Width:** 15 IN

**Weight:**35 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Commercial
- **Amperage Rating:** 320A
- **Feed Type:** Top/bottom
- **Line:** #4-600 kcmil
- **Number Of Jaws:** Four-jaw
- **Phase:** Single-phase
- **Accessories:** Anti-inversion clips
- **Bypass:** Lever
- **Number Of Sockets:** 1
- **Voltage Rating:** 600V

### Supporting documents:

- [Dimensional Drawing - AE #E-1045 SKT 320A 1P HCP](#)
- [Eaton Specification Sheet - 1010468CH](#)

### Certifications:

- UL Listed

**Product compliance:** No Data



