

Eaton 10250T206NC1N-POP

Catalog Number: 10250T206NC1N-POP

10250T, 30.5 mm, Heavy-Duty Watertight/Oiltight, Point-of-purchase packaging, NEMA 3, 3R, 3S, 4, 4X, 12, 13, Standard, Incandescent, full voltage light unit, Red lens, Plastic, 24 Vac/dc supply, #757, 24 Vac/dc lamp

General specifications



Product Name	Catalog Number
Eaton 10250T pushbutton	10250T206NC1N-POP
UPC	Product Length/Depth
782114408537	7 in
Product Height	Product Width
3 in	6 in
Product Weight	Warranty
0.43 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

defaultTaxonomyAttributeLabel

Special features

Point-of-purchase packaging

Type

30.5 mm, Heavy-Duty Watertight/Oiltight

Lamp voltage

24 Vac/dc

Actuator

Standard

LED lamp number

#757

Lens color

Red

Lens material

Plastic

Light unit type

Incandescent, full voltage

Rating

NEMA 3, NEMA 3R, NEMA 3S, NEMA 4, NEMA 4X, NEMA 12,
NEMA 13

Series

10250T

Supply voltage

24 Vac/dc

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T206NC1N-POP](#)

[Quick Selector - 10250T Pilot Devices](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)