



Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty, Assembled Selector Switch

10250T20KB-POP

UPC:782114408506

Dimensions:

- **Height:** 3 IN
- **Length:** 7 IN
- **Width:** 6 IN

Weight: .43 LB

Notes: Includes three different legend plates. Point-of-Purchase Packaging.

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Knob
- **Actuator Color:** Black
- **Contact Configuration:** 1NO-1NC
- **Illumination:** Non-illuminated
- **Legend:** OFF/ON HAND/AUTO RUN/JOG
- **Number Of Positions:** Two-position
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Quick Selector - 10250T Pilot Devices](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked





Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty, Assembled Selector Switch

10250T20KB-POP

UPC:782114408506

Dimensions:

- **Height:** 3 IN
- **Length:** 7 IN
- **Width:** 6 IN

Weight: .43 LB

Notes: Includes three different legend plates. Point-of-Purchase Packaging.

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Knob
- **Actuator Color:** Black
- **Contact Configuration:** 1NO-1NC
- **Illumination:** Non-illuminated
- **Legend:** OFF/ON HAND/AUTO RUN/JOG
- **Number Of Positions:** Two-position
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Quick Selector - 10250T Pilot Devices](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked



