



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T34RPOP Indicating Light - Transformer Type 120 V 50/60HZ

Eaton Corp

Catalog Number	10250T34RPOP
Manufacturer	Eaton Corp
Description	10250T, 30.5 MM, Heavy-Duty Watertight/Oiltight, Point-Of-Purchase Packaging, Nema 3, 3R, 3S, 4, 4X, 12, 13, Standard, Run and Jog, Incandescent, Transformer Light Unit, Red Lens, Plastic, 120 Vac Supply, #757
Weight per unit	0.4300 (lbs/each)
Product Category	Pilot Light Complete Assemblie

Features

dimensions	7.0000 IN X 6.0000 IN X 3.0000 IN
media	Yes

Descriptions

Description	INDICATING LIGHT - TRANSFORMER TYPE 120 V 50/60HZ
extra long description	ETN 10250T34R-POP Indic LGT-trans-m
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	10250T, 30.5 mm, Heavy-Duty Watertight/Oiltight, Point-of-purchase packaging, NEMA 3, 3R, 3S, 4, 4X, 12, 13, Standard, RUN and JOG, Incandescent, transformer light unit, Red lens, Plastic, 120 Vac supply, #757
Product Type	Indic LGT-Trans-Mer Type 120V 50/60HZ (
Special Features	Point-of-purchase packaging

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114408544
Manufacturers Part Number	10250T34R-POP
UPC	782114408544

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON

Packaging

Carton	1
Weight Per each	0.43



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Power

Distribution and Controls

standard

UL Listed, CSA Certified, CE Marked