

defaultTaxonomyAttributeLabel

Special features

Point-of-purchase packaging

Type

30.5 mm, Heavy-Duty Watertight/Oiltight

Legend

RUN and JOG

Actuator

Standard

LED lamp number

#757

Lens color

Red

Lens material

Plastic

Light unit type

Incandescent, transformer

Rating

NEMA 3, NEMA 3R, NEMA 3S, NEMA 4, NEMA 4X, NEMA 12,
NEMA 13

Series

10250T

Supply voltage

120 Vac

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T34R-POP](#)

[Quick Selector - 10250T Pilot Devices](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia