



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 10250T53C 30MM Cont BLK 1NO Amber *Eaton Corp*

Catalog Number	10250T53C
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton Contact Block, 10250T Series, Standard Contact Block, 1NO, Pressure Terminals
Weight per unit	0.0500 (lbs/each)
Product Category	Contact Blocks

### Features

Contact Configuration	1 NO (standard)
media	Yes

### Dimensions and Weight

Depth	1.3
Height	2.1
Width	1.3

### Descriptions

Description	30MM CONT BLK 1NO AMBER
extra long description	ETN 10250T53C 30MM CONT BLK 1NO AMB
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton contact block, 10250T series, Standard Contact Block, 1NO, Pressure terminals
Product Type	30MM Cont BLK 1NO Amber
Special Features	Amber block

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114121450
Manufacturers Part Number	10250T53C
Model	Pushbutton accessory
UPC	782114121450

### Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
----------------------	-------------------------

### Packaging

Carton	1
Weight Per each	0.05



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs Stationary Machinery and Equipment Outside Factory  
- Stationary Machinery and Equipment Outside Factory - Other

standard

UL Listed, CSA Certified, CE Marked