



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T597L 2P III MT Push/Pull FV Order Led Separately W/O Le Eaton Corp

Catalog Number	10250T597L
Manufacturer	Eaton Corp
Description	Eaton 30.5 MM Heavy-Duty Watertight/Oiltight Push-Pull Unit, Class I Division 2, Bayonet Base, Illuminated, Led, Full Voltage, 24 Vac/VDC Light Unit, Two-Position, Maintained Push and Pull, 10250T Series
Weight per unit	0.3900 (lbs/each)
Product Category	Push Button Components

Features

dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
media	Yes

Dimensions and Weight

Height	1
Length	1
Width	1

Descriptions

Description	2P ILL MT PUSH/PULL FV ORDER LED SEPARATELY W/O LE
extra long description	ETN 10250T597L 2P ILL MT P-P FV-LED
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 30.5 mm Heavy-Duty Watertight/Oiltight Push-Pull Unit, Class I Division 2, Bayonet base, Illuminated, LED, full voltage, 24 Vac/Vdc Light Unit, Two-position, Maintained push and pull, 10250T Series
Product Type	2P III MT P-P FV-Led Separly W/O Lens

Manufacturer Information

Brand	Eaton
GTIN	00782114713280
Manufacturers Part Number	10250T597L
UPC	782114713280

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.39

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
standard	UL Listed, CSA Certified, CE Marked