

Eaton 10250T714R

Catalog Number: 10250T714R

10250T, 30.5 mm, Class I Division 2, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Non-illuminated, Two-position, Maintained push and pull, Standard, Red actuator, Plastic bus, 1NO-1NC

General specifications



Product Name
Eaton 10250T pushbutton

UPC
782114505328

Product Height
1 in

Product Weight
0.1 lb

Compliances
CE Marked
FDA 3-A

Catalog Number
10250T714R

Product Length/Depth
1 in

Product Width
1 in

Warranty
1 year

Certifications
UL 1604
CSA Certified
UL 508

defaultTaxonomyAttributeLabel

Type

30.5 mm, Class I Division 2

Actuator color

Red

Bus material

Plastic

Actuator

Standard

Operating mode

Pull: maintained

Push: maintained

Contact configuration

1 NO-1 NC

Illumination

Non-illuminated

Series

10250T

Number of positions

2

Rating

NEMA 4X

NEMA 12

NEC Class I Division 2, Groups B, C and D

NEMA 3R

NEMA 3

NEMA 13

NEMA 4

Size

40 mm

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T714R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)