

Specifications

Eaton 1107LA

Eaton residential grade duplex receptacle, #14-10 AWG, 15A, Decorator, Commercial, Residential, Flush, 125V, Side and push, Light almond, Brass, Impact-resistant thermoplastic, 5-15R, Duplex, Screw, Thermoplastic, Core pack

General specifications

PRODUCT NAME	Eaton residential grade duplex receptacle
CATALOG NUMBER	1107LA
UPC	032664750861
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	3.81 in
PRODUCT WIDTH	0.69 in
PRODUCT WEIGHT	0.01 lb
COMPLIANCES	RoHS Compliant NAFTA
CERTIFICATIONS	UL NOM Federal Specification Classification 6233 01
PRODUCT TYPE	Residential grade

Product specifications

DEVICE TYPE	Receptacle
TYPE	Decorator duplex receptacle
AMPERAGE RATING	15A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
APPLICATION	Commercial/residential
DEVICE GRADE	Standard grade
WIRING METHOD	Side and push
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Decorator
MATERIAL	Thermoplastic
PACKAGING TYPE	Core pack
COLOR	Light almond
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Push-In Terminals Wiring: #14 AWG copper (CU) Only, Side Wiring: #10-14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-15R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Impact-resistant thermoplastic
RECEPTACLE TYPE	Duplex

Resources

MULTIMEDIA	Residential straight blade receptacles
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 1107LA Duplex receptacles spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

