

Eaton 121248 G NK

Catalog Number: 121248 G NK

Eaton B-Line series wireway, 12" height, 48" length, 12" width, G NK wireway, Thru holes, No knockouts, Screw cover, NEMA 1, Steel, Plated screws, ANSI 61 gray, 14 gauge

General specifications



| | |
|-----------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton B-Line series wireway | 121248 G NK |
| UPC | Product Length/Depth |
| 782051107258 | 48 in |
| Product Height | Product Width |
| 12 in | 12 in |
| Product Weight | Certifications |
| 40.076 lb | CSA Certified |
| | UL Listed |

Material/finish

Material thickness

14 gauge

Finish color

ANSI 61 gray

Model

Closure type

Plated screws

Mounting method

Thru holes

Special features

Cover is secured with plated screws

Type

G NK wireway

Resources

Catalogs

[EnviroShield Wireway Flyer](#)

Specifications and datasheets

[Eaton Specification Sheet - 121248 G NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)