



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1224I Switch, Hubpro, 4-Way, 20A 120/277V, Iv *Hubbell Wiring Devices*

Catalog Number	1224I
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Hubbell- Pro Series, Toggleswitches, General Purpose Ac, Four Way, 20A 120/277V Ac, Back and Sidewired, Ivory
Weight per unit	0.0790 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	DPDT
amperage rating	20
connection	Back and Side Wired
Contact Configuration	Two Position
Contact Rating	Per UL 20
Current Rating	20
insulation	False
operating cycles	50,000
pallet quantity	4400
Poles	Double Pole
Switch Type	Toggle
Voltage Rating	120-277
Wattage	5540

### Dimensions and Weight

Size	4.18 in x 1.49 in x 1.83 in
------	-----------------------------

### Descriptions

Description	SWITCH, HUBPRO, 4-WAY, 20A 120/277V, IV
extra long description	HWDK 1224I SWITCH, HUBPRO, 4-WAY, 2
Long Description	Switches and Lighting Controls, Hubbell- PRO Series, ToggleSwitches, General Purpose AC, Four Way, 20A 120/277V AC, Back and SideWired, Ivory
Product Type	Switch, Hubpro, 4-Way, 20A 120/277V, Iv
Special Features	Standard Product

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585835365
Manufacturers Part Number	1224I
series	Heavy Duty
UPC	783585835365



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	TOGGLE

## Packaging

Carton	1
Package	10
Weight Per each	0.079

## Uses, Certifications, and Standards

Application	Back and Side Wired
Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed