

---

## MANUAL CONTROLLER

1225I | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Single Pole, Double Throw Switch, 20 amps, 120/277 volts, Ivory.



- Oversize silver alloy contacts for long life and better heat dissipation.
- Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
- Fiber terminal insulation barriers standard.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Bodies, covers, and toggles molded of durable nylon.
- Single Pole-Double Throw only.
- Locking Switches supplied with one 1498-NT key.
- Normally open.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Type: Maintained Contact  
Number Of Poles: 1  
Special Features: Two Circuit

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: Yes  
UL Listing No: Yes

UN SPSC: 39121507

## DIMENSIONS

Depth (US): 1.469"

Height (US): 3.281"

Width (US): 1.5"

Weight: 0.26408

## TECHNICAL INFORMATION

Amps: 20A

Volts: 120/277VAC

Volts (AC): 120/277

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

