

Eaton 1234-BOX

Catalog Number: 1234-BOX

Eaton power device receptacle, #12 - 4 AWG, 30A, Flush, 250V, Back, Black, NEMA 6-30R, Two-pole, Three-wire, Two-pole, three-wire, grounding, Screw, Glass-filled nylon, Power, Used with S42

General specifications



Product Name

Eaton power device receptacle

Catalog Number

1234-BOX

UPC

032664306303

Product Length/Depth

2.25 in

Product Height

3.88 in

Product Width

2.38 in

Product Weight

0.36 lb

Compliances

RoHS Compliant
NAFTA

Certifications

UL Listed
NOM
CSA Certified

defaultTaxonomyAttributeLabel

Used with

S42

Amperage Rating

30A

Voltage rating

250 V

Wiring method

Back

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Color

Black

Connection type

Screw

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

6-30R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 1234-BOX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton 1234-BOX

Catalog Number: 1234-BOX

Eaton power device receptacle, #12 - 4 AWG, 30A, Flush, 250V, Back, Black, NEMA 6-30R, Two-pole, Three-wire, Two-pole, three-wire, grounding, Screw, Glass-filled nylon, Power, Used with S42



General specifications

| | |
|-------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton power device receptacle | 1234-BOX |
| UPC | Product Length/Depth |
| 032664306303 | 2.25 in |
| Product Height | Product Width |
| 3.88 in | 2.38 in |
| Product Weight | Compliances |
| 0.36 lb | RoHS Compliant |
| | NAFTA |
| Certifications | |
| UL Listed | |
| NOM | |
| CSA Certified | |

defaultTaxonomyAttributeLabel

Used with

S42

Amperage Rating

30A

Voltage rating

250 V

Wiring method

Back

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Color

Black

Connection type

Screw

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

6-30R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 1234-BOX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)