



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1250L SW Moment Control 15A 120/277V Lock Gy

*Pass & Seymour/Legrand*

Catalog Number	1250L
Manufacturer	Pass & Seymour/Legrand
Description	Locking Manual Controller, Single-Pole, Double-Throw Switch. 15A, 120/277VAC Rating, Tested to 3A, 24VDC Rating.
Weight per unit	0.2750 (lbs/each)
Product Category	Manual Motor Switches & Accy.

### Features

amperage rating	15
Contact Configuration	NO
Contact Rating	15amp, 120/277vac
insulation	Bare
Poles	spdt
Voltage	120.0 V
Voltage Rating	120/277
Wattage	1
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Color	Locking
Finish	Matte

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	SW MOMENT CONTROL 15A 120/277V LOCK GY
extra long description	P&S 1250L SW MOMENT CNTRL 15A 120/
Long Description	Locking Manual Controller, Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating, Tested to 3A, 24VDC rating.
Product Type	SW Moment CNTRL 15A 120/277V Lock Gy
Special Features	Oversized silver alloy contacts, side wired, can be mounted in standard device box\

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007125023
Manufacturers Part Number	1250-L
UPC	785007125023

### Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Manual Controller Switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 15.0

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.275

## Uses, Certifications, and Standards

Application ..... Industrial

Enclosure ..... Box or NEMA 1 sheet steel

Mounting ..... WALL

standard ..... UL Listed