Pass and Seymour
20A Single Pole, Double Throw Ivory
Part No. 1251I



Single-Pole, Double-Throw Manual Control Switch, 20A, 120/277V.

Features & Benefits

- Oversize silver alloy contacts for long life and better heat dissipation.
- Fiber terminal insulation barriers standard.
- Bodies, covers, and toggles molded of durable nylon.
- Locking Switches supplied with one 1498-NT key.
- For covering patents, see www.legrand.us/patents.
- Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Single Pole-Double Throw and Double Pole-Double Throw.
- Normally open.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007125115
Country Of Origin	Mexico	Material	Thermoplastic
Features	Durable	Switch Type	Toggle
Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 498

Warranty Type	1-Year Limited Warranty	Type	Manual Controller

Dimensions

Product Width US	1.5 in	Product Depth US	1.469 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17949		

Technical Information

Load Rating	20 A @ 120/277 VAC	Connection Location	Side Only
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Double Throw	Amperage	20 A
Number of Poles	Single Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120/277 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		