

Eaton 1254-BOX

Catalog Number: 1254-BOX

Eaton power device receptacle, #12 - 4 AWG, 50A, Flush, 250V, Back, Black, NEMA 6-50R, Two-pole, Three-wire, Two-pole, three-wire, grounding, Screw, Glass-filled nylon, Power, Used with A42

Photo is representative

General specifications

| | |
|-------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton power device receptacle | 1254-BOX |
| UPC | Product Length/Depth |
| 032664306709 | 3.88 in |
| Product Height | Product Width |
| 2.25 in | 2.94 in |
| Product Weight | Compliances |
| 0.35 lb | RoHS Compliant |
| | NAFTA |
| Certifications | |
| CSA Certified | |
| UL Listed | |



defaultTaxonomyAttributeLabel

Used with

A42

Amperage Rating

50 A

Voltage rating

250 V

Wiring method

Back

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Color

Black

Connection type

Screw

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

6-50R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 1254-BOX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia