

# Eaton 14128-SDFQR

Catalog Number: 14128-SDFQR

Eaton B-Line series JIC panel enclosure, 15.49" height, 8.34" length, 13.86" width, NEMA 4X, Hinged cover, SDFQR enclosure, Wall mount, Medium single door, Optional external mounting feet, Fiberglass, Seamless poured in-place gasket



## General specifications

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	14128-SDFQR
UPC	Product Length/Depth
782051524314	8.34 in
Product Height	Product Width
15.49 in	13.86 in
Product Weight	Certifications
9.5 lb	UL 50
	NEMA
	CSA C22.2.

## Material/finish

### Material

Fiberglass

### Finish color

Unfinished

### Color

Gray

## Model

### Style

Medium single door

### Model

SDFQR enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

Optional external mounting feet

### Locking provisions

Padlock provision

### Closure type

Hinged

### Special features

Stainless pull drawn catch

## Standards

### NEMA Rating

4X

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 14128-SDFQR](#)