



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1450 1/2" Ins STR Conn *Crouse-Hinds*

Catalog Number	1450
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Emt Set Screw Type Connector, Emt, Straight, Insulated, Steel, 1/2"
Weight per unit	0.0800 (lbs/each)
Product Category	Steel Insulated Straight Set S

### Features

connection	Threaded
dimensions	1.5000 IN X 0.8800 IN X 0.8800 IN

### Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

### Dimensions and Weight

Size	1/2 in
------	--------

### Descriptions

Description	1/2" INS STR CONN
extra long description	MIDWEST 1450 1/2 EMT SS CONN INSULA
Features	Crouse-Hinds series EMT connectors and couplings are used to join EMT conduit to a box or enclosure, or to couple two ends of EMT conduit. Our EMT fittings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in steel and zinc die cast. Crouse-Hinds series EMT connectors and couplings are also available painted in seven different colors to better match architectural specifications and preferences.
Long Description	Eaton Crouse-Hinds series EMT set screw type connector, EMT, Straight, Insulated, Steel, 1/2"
Product Type	1/2 Emt SS Conn Insulated

### Manufacturer Information

Brand	Eaton
GTIN	00784564114501
Manufacturers Part Number	1450
UPC	784564114501

### Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	Set screw type connector



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	50
Package	200
Weight Per each	0.08

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL