

Watertight Rubber Housing Plug, Yellow

14W47



Straight Blade Watertight Plug 15amp
125volt 5-15p



features & benefits

- Rubber body construction stands up to impacts, oils, chemicals, heat, and weather.
- Floating blades allow self-alignment with contacts for a firm, even electrical connection.
- Terminal screws backed-out, ready-to-wire, saving time and money.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Compression-type cord grip provides watertight seal and 205 lb. pull out strength.
- Multiple ring seals between plug and connector ensures protection from water and contaminants.
- Quick-drive assembly screws allow for fast installation, saving time and money.
- NEMA 4, 4X, Watertight. IP65, 66, 67. Rated watertight for 1,000 psi high-pressure hose-down.

specifications

General Info

Color: yellow
Type: Plug

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42M

CSA Standard: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: E146159
UL Standard: Yes
UN SPS C: 39121402
UR: No

Dimensions

Diameter U S: 1.85"
Length U S: 2.62"

Technical Information

Volts A C: 125

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant