

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301410031](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Connector, 2 Pole/3 Wire, NEMA 5-15, 125V

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Wiring Devices
 Series [130141](#)
 IP Rating N/A
 NEMA Configuration NEMA 5-15
 Overview [Heavy-Duty Industrial Wiring Devices](#)
 Product Literature Order No 987650-8068
 Product Name Super-Safeway
 Receptacle Type Single
 Specialty N/A
 Type Connector
 UPC 78678870302
 Woodhead Yes

Physical

Flange No
 Flip Lid No
 Gender Female
 Length N/A
 Locking Blade No
 Net Weight 113.398/g
 Poles 2-pole/3-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V

Material Info

Engineering Number 1547



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/108/2014 (17 Dec
 2014)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Reviewed

Search Parts in this Series

[130141](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301410031](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Connector, 2 Pole/3 Wire, NEMA 5-15, 125V

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Wiring Devices
 Series [130141](#)
 IP Rating N/A
 NEMA Configuration NEMA 5-15
 Overview [Heavy-Duty Industrial Wiring Devices](#)
 Product Literature Order No 987650-8068
 Product Name Super-Safeway
 Receptacle Type Single
 Specialty N/A
 Type Connector
 UPC 78678870302
 Woodhead Yes

Physical

Flange No
 Flip Lid No
 Gender Female
 Length N/A
 Locking Blade No
 Net Weight 113.398/g
 Poles 2-pole/3-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V

Material Info

Engineering Number 1547



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 ED/108/2014 (17 Dec
 2014)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130141 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION