



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1594TC2M 15A Port Gfci 2' Tri Conn Man Reset *Pass & Seymour/Legrand*

Catalog Number	1594TC2M
Manufacturer	Pass & Seymour/Legrand
Description	Portable Ground Fault Circuit Interrupter, 15AMP 125VOLT, 2' Tri-Cord Connector, Manual Reset
Weight per unit	1.4 (lbs/each)
Product Category	Portable Cord Sets

Features

amperage rating	15
connection	60Hz
Material	Thermoplastic
media	Yes
Poles	2
trip range	5+1mA
Trip Type	.025sec
Voltage Rating	125

Dimensions and Weight

Height	2.9"
Length	10.3"
Width	3.5"

Descriptions

Description	15A PORT GFCI 2' TRI CONN MAN RESET
extra long description	P&S 1594TC2M 15A PORT GFCI 2' TRI C
Long Description	Portable Ground Fault Circuit Interrupter, 15amp 125volt, 2' Tri-Cord Connector, Manual Reset
Product Type	15A Port Gfci 2' Tri Conn Man Reset
Special Features	Durable, open neutral protection,

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007263893
Manufacturers Part Number	1594TC2M
UPC	785007263893

Taxonomies, Classifications, and Categories

Category Description	Industrial GFCI devices
Type	Portable GFCI Plug

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	1.445

Uses, Certifications, and Standards

Application	Commercial
Enclosure	Bare
Frequency Rating	60 Hz
Operating Temperature	-35C(-30F) to +66C(150F)
standard	UL 943/498