


# GFCIs

## Audible Alarm GFCI Receptacles 2 Pole, 3 Wire Grounding 15 & 20A, 125VAC




### Features

- Audible Alarm alert of tripped condition. Alarm can be turned ON/OFF.
- Alarm rated at 60 db at 10 feet.
- Rated as a 1.5 HP motor control switch.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Feed-thru wiring configuration allows GFCI to protect downstream receptacles.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 10kA short circuit rating.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

### Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity
- Trio Threshold: 5± 1mA

CATALOG NUMBER	RATING		COLOR	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE		
	A.	VAC			UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
<b>TRADEMASTER® AUDIBLE ALARM TAMPER-RESISTANT DUPLEX GFCI</b>							
1595TRAI	15	125	Ivory	5-15R	•	•	•
1595TRAW	15	125	White	5-15R	•	•	•
1595TRA	15	125	Brown	5-15R	•	•	•
1595TRABK	15	125	Black	5-15R	•	•	•
1595TRALA	15	125	Light Almond	5-15R	•	•	•
<b>SPECIFICATION GRADE AUDIBLE ALARM TAMPER-RESISTANT DUPLEX GFCI</b>							
2095TRAI	20	125	Ivory	5-20R	•	•	•
2095TRAW	20	125	White	5-20R	•	•	•
2095TRA	20	125	Brown	5-20R	•	•	•
2095TRAGRY	20	125	Gray	5-20R	•	•	•
2095TRABK	20	125	Black	5-20R	•	•	•
2095TRARED	20	125	Red	5-20R	•	•	•
2095TRALA	20	125	Light Almond	5-20R	•	•	•
<b>HOSPITAL GRADE AUDIBLE ALARM TAMPER-RESISTANT DUPLEX GFCI</b>							
1595HGTRA	15	125	Brown	5-15R	•	•	•
1595HGTRAGRY	15	125	Gray	5-15R	•	•	•
1595HGTRALA	15	125	Light Almond	5-15R	•	•	•
2095HGTRAI	20	125	Ivory	5-20R	•	•	•
2095HGTRAW	20	125	White	5-20R	•	•	•
2095HGTRARED	20	125	Red	5-20R	•	•	•
2095HGTRALA	20	125	Light Almond	5-20R	•	•	•



### National Electrical Code® Section 406.12 Tamper-Resistant Receptacles in Dwelling Units.

In all areas specified in 210.52 all 125-volt, 15- and 20-amp receptacles shall be listed tamper-resistant receptacles.

All devices listed on this page conform to NEMA WD-1 and WD-6.


# DEVICES & WALL PLATES

## Color Selection Chart

### Devices & Plastic Wall Plate Colors



Ivory    Light Almond    White    Green    Antique Brass    Dark Bronze    Nickel



Black    Blue    Brown    Gray    Orange    Red

See specific device and wall plate catalog charts for particular color availabilities.

### Metal Wall Plates


Metal Finish




Aluminum    Brass (Brushed)    Polished Brass    Stainless Steel    Brushed Bronze    Chrome

### Custom Metal Wall Plates Paint Finish Colors

Paint Color



Orange    Green    Gray    Yellow    Glossy Black    Brown    White



Primer    Red    Pink    Flat Black    Ivory    Light Almond    Blue

To order custom metal wall plates, see Pages P-40 – P-42.  
**For additional colors consult factory.**