
20A, 125V WATERTIGHT STRAIGHT BLADE CONNECTOR, YELLOW

15W33 | [Pass & Seymour](#)



FEATURES & BENEFITS

Rated watertight for 1,500 psi high-pressure hosedown, P&S plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Yellow
Type: Connector
Features: Watertight
Number Of Poles: 2
Number Of Wires: 3
Special Features: Watertight

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: LR701645
CSA Listed: Yes
CSA Standard: Yes
Federal Spec: Yes
UL Listing No: E146159
UL Standard: Yes
UN SPSC: 39121402

DIMENSIONS

Diameter (US): 1.81"
Length (US): 4.01"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 5-20R
NEMA Rating: 4X/6P
Volts: 125V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

