

Eaton 16128-SDSS4

Catalog Number: 16128-SDSS4

Eaton B-Line series wall mounted panel enclosure, 16" height, 8" length, 16" width, NEMA 4X, Hinged cover, SDSS4 enclosure, Wall mount, Medium single door, Thru holes, opt. external mounting feet, 304 stainless, Seamless poured in-place gasket

Product specifications



Special features

Stainless 1/4 turn latches

Finish color

#4 brushed

Wall thickness

16 gauge, 16 gauge

Mounting method

Wall

Cover type

Hinged

NEMA Rating

4X

Style

Medium single door

Closure type

Hinged

Color

Gray

Material

304 stainless steel

Country of origin

US

Mounting hole details

Thru holes, optional external mounting feet

Model

SDSS4 enclosure

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 16128-SDSS4](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)