

# Eaton 16168-SD

Catalog Number: 16168-SD

Eaton B-Line series wall mounted panel enclosure, 16" height, 8" length, 16" width, NEMA 4, Hinged cover, SD enclosure, Wall mount, Medium single door, Thru holes, optional external mounting feet, Carbon steel, Seamless poured in-place gasket

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series wall mounted panel enclosure	16168-SD
	<b>UPC</b>
	782051091861
<b>Product Length/Depth</b>	<b>Product Height</b>
8 in	16 in
<b>Product Width</b>	<b>Product Weight</b>
16 in	23.2 lb

## Certifications

UL 50  
CSA C22.2.  
NEMA

## defaultTaxonomyAttributeLabel

### Country of origin

US

### Special features

1/4 turn latches

### Style

Medium single door

### Finish color

Painted

### Color

ANSI 61 gray

### NEMA Rating

4

### Cover type

Hinged

### Wall thickness

16 gauge, 16 gauge

### Material

Carbon steel

### Model

SD enclosure

### Mounting method

Wall

### Closure type

Hinged

### Mounting hole details

Thru holes, optional external mounting feet

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 16168-SD](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)