



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1652 1" STL Insldt Emt STRT CMP Conn

Crouse-Hinds

| | |
|------------------|--|
| Catalog Number | 1652 |
| Manufacturer | Crouse-Hinds |
| Description | Emt Compression Connector, 1 In Trade Size, Straight Connection Orientation, Zinc Plated, Insulated, 1.69 In Length, 1.58 In Diameter, 0.64 In Thread Length, 0.22 LB/Ea |
| Weight per unit | 0.2200 (lbs/each) |
| Product Category | Steel Insulated Straight Compr |

Features

| | |
|------------|-----------------------------------|
| dimensions | 1.2500 IN X 1.6900 IN X 1.6900 IN |
|------------|-----------------------------------|

Material, Color, and Finish

| | |
|--------|-------------|
| Finish | Zinc Plated |
|--------|-------------|

Dimensions and Weight

| | |
|------|------|
| Size | 1 in |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 1" STL INSLTD EMT STRT CMP CONN |
| extra long description | MIDWEST 1652 1 EMT CMP CONN INSULAT |
| Features | Crouse-Hinds series EMT connectors and couplings are used to join EMT conduit to a box or enclosure, or to couple two ends of EMT conduit. Our EMT fittings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in steel and zinc die cast. Crouse-Hinds series EMT connectors and couplings are also available painted in seven different colors to better match architectural specifications and preferences. |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Eaton |
| GTIN | 00784564116529 |
| UPC | 784564116529 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------|
| Category Description | STEEL EMT FITTINGS |
| Type | Compression Connector |

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Package | 100 |
| Weight Per each | 0.22 |

Uses, Certifications, and Standards

| | |
|----------|---------|
| standard | UL, cUL |
|----------|---------|