



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



168020 1/2" Super Hawg (Tool Only)

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 168020 |
| Manufacturer | Milwaukee Electric Tool |
| Description | The 1/2 In. Super Hawg Has Power and Speed For Drilling Holes Of All Sizes In Wood Frame Construction. The 13 Amp Motor Has Two Operating Speeds Of 1750 and 450 RPM With A Clutch In The Low Gear Range. Speed Shifting Is Easy. The Comfort Grip Roto-Lok Handle Features 3 Positions With 90 Degree Left-Right Rotation For Maximum Operator Comfort For All Applications. |
| Weight per unit | 16.3 (lbs/each) |
| Product Category | Power Tools - Corded |

Features

| | |
|-----------------------------|---------|
| Cord Length | 8.0 |
| idea granular category code | 2288 |
| Switch Type | Trigger |
| Voltage | 120.0 |

Material, Color, and Finish

| | |
|------------------|-------|
| Handle Material | Metal |
| Housing Material | Metal |

Dimensions and Weight

| | |
|--------|------|
| Height | 5.25 |
| Length | 8.0 |
| Width | 25.5 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 1/2" SUPER HAWG (TOOL ONLY) |
| extra long description | MILW 1680-20 Super Hawg Drill |
| Features | 1/2 in. Super Hawg Drill |
| Long Description | The 1/2 in. Super Hawg has power and speed for drilling holes of all sizes in wood frame construction. The 13 amp motor has two operating speeds of 1750 and 450 RPM with a clutch in the low gear range. Speed shifting is easy. The comfort grip Roto-Lok handle features 3 positions with 90 degree left-right rotation for maximum operator comfort for all applications. |
| Product Type | Super Hawg Drill |
| Short Description | Super Hawg Drill |
| Special Features | Features: Clutch In Low Speed; High Operating Speeds For Maximum Productivity; 90 DEG Left-Right; Roto-Lok Handle For Maximum Operating Comfort; Easy Turn Gear Shift Knob; Comfort Grip Switch Handle And Gear Case With Front T-Bar Handle; Chuck Type: Keyed; Cord Type: 8 FT Fixed; Tool Weight: 14.700 LB; Capacity In Wood: 6 IN Hole Saw; Spindle Lock: No; Metal Capacity: 1/2 IN Twist Bit; Spindle Size: 5/8-16 IN; Gear Train: Triple; Construction Type: Grounded; Length: 22 IN; Clutch: |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242001972 |
| Manufacturers Part Number | 1680-20 |
| UPC | 045242001972 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------|
| Category Description | POWER TOOLS |
| Type | Super Hawg Drill |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight | 14.7 |
| Weight Per each | 16.335 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | For Drilling Holes Of All Sizes In Wood Frame Construction |
|-------------|--|