

Eaton 181610-SDFQR

Catalog Number: 181610-SDFQR

Eaton B-Line series JIC panel enclosure, 19.77" height, 10.34" length, 18.15" width, NEMA 4X, Hinged cover, SDFQR enclosure, Wall mount, Medium single door, Optional external mounting feet, Fiberglass, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	181610-SDFQR
UPC	Product Length/Depth
782051524338	10.34 in
Product Height	Product Width
19.77 in	18.15 in
Product Weight	Certifications
16 lb	UL 50
	NEMA
	CSA C22.2.

Material/finish

Material

Fiberglass

Finish color

Unfinished

Color

Gray

Model

Style

Medium single door

Model

SDFQR enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

Optional external mounting feet

Locking provisions

Padlock provision

Closure type

Hinged

Special features

Stainless pull drawn catch

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 181610-SDFQR](#)