

# PHOTOCONTROLS

## 1/2" Conduit Mount

### 180° Swivel, Lexan® Housing

#### 2001 Series



#### SPECIFICATIONS

- **ON/OFF:** Turn ON is 1 to 5fc, Turn OFF is 3 to 15fc, without the slide in position. ON/OFF adjustment is easily made by moving a slide cover. No tools required.
- **Time Delay:** ON and OFF.
- **Cell:** Cadmium sulphide, epoxy conformal coated 1/2" diameter.
- **Contacts:** Remain closed between dusk and dawn. (The unit fails in the ON position).
- **Lead Wires:** Three color coded, minimum 6" wire leads, #16AWG, rated for 105 °C.
- **Power Consumption:** Averages under 1 watt.
- **Temperature Range:** -40 °F to +140 °F (-40 °C to +60 °C).
- **Fail Mode:** ON.
- **Warranty:** 5 years.

#### APPLICATIONS

- Flood Lamp.
- Patio Lamp.
- Decorative lighting.

#### FEATURES

- **Sensor:** Conformal coated cadmium sulphide photocell resists effects of moisture and airborne contaminants. Photocell responds to the light spectrum near to that of a human eye.
- **Operation:** Delay of up to two minutes to prevent false switching due to light from passing vehicles, lightning, etc.
- **Standards:** Meets ANSI/UL773A.
- **Housing:** All Lexan® enclosures are impact and vandal resistant. Translucent Lexan® Dome prolongs cell life by further screening out ultraviolet rays. Dome and base are ultrasonically welded for maximum strength.
- **Energy Savings:** Works with screw base CFLs.

#### ACCESSORIES

- **73866:** See page 434.

#### ACCESSORY

73866



CAT. NO.	CERTIFICATION	UPC CODE	VOLTAGE VAC 50/60Hz	RATING		
				TUNGSTEN	BALLAST	LED
2001	cULus	60015	120	2000W	1800VA	600VA
2002	cULus	60016	208-277	3470-4620W	2080-2770VA	1040-1385VA
2006	CSA	60028	347	5760W	3470VA	—
2018	—	62021	480	7500W	4800VA	—

# PHOTOCONTROLS

## 1/2" Conduit Mount

### 180° Swivel, Lexan® Housing

#### 2001 Series



#### SPECIFICATIONS

- **ON/OFF:** Turn ON is 1 to 5fc, Turn OFF is 3 to 15fc, without the slide in position. ON/OFF adjustment is easily made by moving a slide cover. No tools required.
- **Time Delay:** ON and OFF.
- **Cell:** Cadmium sulphide, epoxy conformal coated 1/2" diameter.
- **Contacts:** Remain closed between dusk and dawn. (The unit fails in the ON position).
- **Lead Wires:** Three color coded, minimum 6" wire leads, #16AWG, rated for 105 °C.
- **Power Consumption:** Averages under 1 watt.
- **Temperature Range:** -40 °F to +140 °F (-40 °C to +60 °C).
- **Fail Mode:** ON.
- **Warranty:** 5 years.

#### APPLICATIONS

- Flood Lamp.
- Patio Lamp.
- Decorative lighting.

#### FEATURES

- **Sensor:** Conformal coated cadmium sulphide photocell resists effects of moisture and airborne contaminants. Photocell responds to the light spectrum near to that of a human eye.
- **Operation:** Delay of up to two minutes to prevent false switching due to light from passing vehicles, lightning, etc.
- **Standards:** Meets ANSI/UL773A.
- **Housing:** All Lexan® enclosures are impact and vandal resistant. Translucent Lexan® Dome prolongs cell life by further screening out ultraviolet rays. Dome and base are ultrasonically welded for maximum strength.
- **Energy Savings:** Works with screw base CFLs.

#### ACCESSORIES

- **73866:** See page 434.

#### ACCESSORY

73866



CAT. NO.	CERTIFICATION	UPC CODE	VOLTAGE VAC 50/60Hz	RATING		
				TUNGSTEN	BALLAST	LED
2001	cULus	60015	120	2000W	1800VA	600VA
2002	cULus	60016	208-277	3470-4620W	2080-2770VA	1040-1385VA
2006	CSA	60028	347	5760W	3470VA	—
2018	—	62021	480	7500W	4800VA	—