
































**BI-METAL RECIPROCATING SAW BLADES (CONTINUED)**

| TPI | LENGTH x WIDTH x THICKNESS |               | 1-PACK      | 5-PACK     | 25-PACK    | 50-PACK      | APPLICATION   |  |
|-----|----------------------------|---------------|-------------|------------|------------|--------------|---|---|
|     | IN                         | MM            | PROD NO     | PROD NO    | PROD NO    | PROD NO      |   |   |
| 14  | 3-5/8 x 5/16 x .035        | 92 x 8 x .9   | —           | 20520314RC | —          | —            |    | •   |
| 14  | 4 x 3/4 x .035             | 102 x 19 x .9 | 20551S414R  | 20550414R  | 20488B414R | 227600SB414R |    | •   |
| 14  | 6 x 3/4 x .035             | 152 x 19 x .9 | 20565S614R  | 20564614R  | 20494B614R | 227560SB614R |   | •   |
| 14  | 8 x 3/4 x .035             | 203 x 19 x .9 | —           | 21519814R  | —          | —            |  | •   |
| 18  | 3-5/8 x 5/16 x .035        | 92 x 8 x .9   | 20522S318RC | 20521318RC | —          | —            |  | •   |
| 18  | 4 x 3/4 x .035             | 102 x 19 x .9 | 20553S418R  | 20552418R  | 20489B418R | 227590SB418R |  | •   |
| 18  | 6 x 3/4 x .035             | 152 x 19 x .9 | 20567S618R  | 20566618R  | 20529B618R | 227510SB618R |  | •   |
| 18  | 8 x 3/4 x .035             | 203 x 19 x .9 | 20563S818R  | 20578818R  | 20487B818R | 227540SB818R |  | •   |
| 18  | 12 x 3/4 x .035            | 305 x 29 x .9 | —           | 21510118R  | 21511B118R | —            |  | •   |
| 24  | 4 x 3/4 x .035             | 102 x 19 x .9 | 20555S424R  | 20554424R  | 20490B424R | —            |  | •   |
| 24  | 6 x 3/4 x .035             | 152 x 19 x .9 | 20569S624R  | 20568624R  | 20496B624R | 227570SB624R |  | •   |
| 24  | 8 x 3/4 x .035             | 203 x 19 x .9 | —           | 20579824R  | —          | —            |  | •   |

**ICON REFERENCE CHART**

|   |   |   |   |   |  |   |   |
|---|---|---|---|---|--|---|---|
| WOOD  | NAIL-EMBEDDED WOOD  | CONTOUR WOOD  | PLASTIC   | THICK METAL   | MEDIUM METAL   | THIN METAL  | NON-FEROUS METAL  |
|  |  |  |  |  |  |  |  |
| DEMOLITION  | FIRE & RESCUE   | PLASTER & DRYWALL   | CAST IRON   | CEMENT BOARD  | TILE   | ABRASIVES   | NATURAL STONE   |
|  |  |  |  |  |  |  |  |