



## #6TS 2.5 in Rigid/EMT Conduit Hanger

By Raco  
Catalog # 2057

#6TS 2.5 in Rigid/EMT Conduit Hanger



\*Representative Image

### Features

- Furnished with nut and bolt to speed installation
- Pregalvanized finish provides corrosion protection
- Additional sizes available

### Application

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls

### General

Hanger Size	6
Material	Steel
UPC	050169020579

### Dimensions

Dimensions	4.437 in x 1.25 in x 3.12 in
EMT Size	2.5 in
Height	3.12 in
Length	4.437 in
Rigid/IMC Size	2.5 in
Trade Size	6
Weight	0.315 lb
Width	1.25 in

### Certifications And Compliance

Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2500

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195968-1](#)  
[Sales Drawings - HANGER WITH BOLT CUS](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-2057-SPEC-EN | REV 5/2024