


# STRAIGHT BLADE RECEPTACLES

## Tamper-Resistant GFCI Receptacles 2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1595TRW

2095TRSW


### Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Feed-thru wiring configuration allows GFCI to protect downstream receptacles.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 - #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 10 kA short circuit rating.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate (except NI, AB, and DB models).
- Tri-drive screws.

### Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

| CATALOG NUMBER  | RATING |     | COLOR         | NEMA CONFIG. NO. | 3rd PARTY COMPLIANCE              |                                      |            |
|---|--------|-----|---------------|------------------|-----------------------------------|--------------------------------------|------------|
|   | A.     | VAC |               |                  | UL <sup>®</sup> 498 C22.2 No. 144 | cUL <sup>us</sup> cULus C22.2 No. 42 | FSUL WC596 |
| <b>TRADEMASTER®/SPEC GRADE TAMPER-RESISTANT 15 AMP DUPLEX GFCI</b>                  |        |     |               |                  |                                   |                                      |            |
| 1595TRI   | 15     | 125 | Ivory         | 5-15R            | •                                 | •                                    | •          |
| 1595TRW   | 15     | 125 | White         | 5-15R            | •                                 | •                                    | •          |
| 1595TR  | 15     | 125 | Brown         | 5-15R            | •                                 | •                                    | •          |
| 1595TRBK  | 15     | 125 | Black         | 5-15R            | •                                 | •                                    | •          |
| 1595TRLA  | 15     | 125 | Light Almond  | 5-15R            | •                                 | •                                    | •          |
| 1595TRNICC4   | 15     | 125 | Nickel        | 5-15R            | •                                 | •                                    | •          |
| 1595TRABCC4   | 15     | 125 | Antique Brass | 5-15R            | •                                 | •                                    | •          |
| 1595TRDBCC4   | 15     | 125 | Dark Bronze   | 5-15R            | •                                 | •                                    | •          |
| <b>TRADEMASTER®/SPEC GRADE TAMPER-RESISTANT 15 AMP DUPLEX GFCI WITH AUTO-GROUND</b> |        |     |               |                  |                                   |                                      |            |
| 1595TRSI  | 15     | 125 | Ivory         | 5-15R            | •                                 | •                                    | •          |
| 1595TRSW  | 15     | 125 | White         | 5-15R            | •                                 | •                                    | •          |
| 1595TRSLA   | 15     | 125 | Light Almond  | 5-15R            | •                                 | •                                    | •          |
| <b>SPECIFICATION GRADE TAMPER-RESISTANT 20 AMP DUPLEX GFCI</b>                      |        |     |               |                  |                                   |                                      |            |
| 2095TRI   | 20     | 125 | Ivory         | 5-20R            | •                                 | •                                    | •          |
| 2095TRW   | 20     | 125 | White         | 5-20R            | •                                 | •                                    | •          |
| 2095TR  | 20     | 125 | Brown         | 5-20R            | •                                 | •                                    | •          |
| 2095TRGRY   | 20     | 125 | Gray          | 5-20R            | •                                 | •                                    | •          |
| 2095TRBK  | 20     | 125 | Black         | 5-20R            | •                                 | •                                    | •          |
| 2095TRRED   | 20     | 125 | Red           | 5-20R            | •                                 | •                                    | •          |
| 2095TRLA  | 20     | 125 | Light Almond  | 5-20R            | •                                 | •                                    | •          |
| <b>SPECIFICATION GRADE TAMPER-RESISTANT 20 AMP DUPLEX GFCI WITH AUTO-GROUND</b>     |        |     |               |                  |                                   |                                      |            |
| 2095TRSI  | 20     | 125 | Ivory         | 5-20R            | •                                 | •                                    | •          |
| 2095TRSW  | 20     | 125 | White         | 5-20R            | •                                 | •                                    | •          |
| 2095TRSLA   | 20     | 125 | Light Almond  | 5-20R            | •                                 | •                                    | •          |



National Electrical Code® Section 406.12 Tamper-Resistant Receptacles in Dwelling Units.

In all areas specified in 210.52 all 125-volt, 15- and 20-amp receptacles shall be listed tamper-resistant receptacles.


# DEVICES & WALL PLATES

## Color Selection Chart

### Devices & Plastic Wall Plate Colors



Ivory    Light Almond    White    Green    Antique Brass    Dark Bronze    Nickel




Black    Blue    Brown    Gray    Orange    Red

See specific device and wall plate catalog charts for particular color availabilities.

### Metal Wall Plates


Metal Finish



Aluminum    Brass (Brushed)    Polished Brass    Stainless Steel    Brushed Bronze    Chrome

### Custom Metal Wall Plates Paint Finish Colors

Paint Color



Orange    Green    Gray    Yellow    Glossy Black    Brown    White



Primer    Red    Pink    Flat Black    Ivory    Light Almond    Blue

To order custom metal wall plates, see Pages P-40 – P-44.

**For additional colors consult factory.**