



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2097HGW Self-Test Gfci Hos GRD Recep 20A 12 W *Pass & Seymour/Legrand*

Catalog Number	2097HGW
Manufacturer	Pass & Seymour/Legrand
Description	20A 125V Self Test Gfci Hospital Grade White
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
interrupt rating	4 to 6 mA
Material	Thermoplastic
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

Dimensions and Weight

Height	4.2
Length	1.03
Width	1.73

Descriptions

Description	SELF-TEST GFCI HOS GRD RECEP 20A 12 W
extra long description	P&S 2097HGW SELF-TEST GFCI HOS GRD
Long Description	20A 125V Self Test GFCI Hospital Grade White
Product Type	Self-Test Gfci Hos GRD Recep 20A 12 W
Special Features	Pass & Seymour invented the GFCI receptacle, and at Legrand, we're constantly reinventing it to ensure the highest level of safety possible. From the most advanced self-testing device to audible alarms to nightlight combos, we're continuously resetting the bar on GFCI innovation and safety.

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007035896
Manufacturers Part Number	2097HGW
UPC	785007035896

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Hospital Grade 20A Self Test Duplex GFCI



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Commercial/Residential
environmental conditions	95% Humidity, UL 94 V2
Frequency Rating	60 Hz
Operating Temperature	-35°C to +66°C
standard	cULus, UL Listed, FSUL