



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



20MR16FL35C(BAB) 20W MR16 Lamp

Sylvania-Ledvance

Catalog Number	20MR16FL35C(BAB)
Manufacturer	Sylvania-Ledvance
Description	Tungsten Halogen Tru Aim MR16 Standard Axial Filament Uv Filter Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 20WATT 12VOLT Flood Beam
Weight per unit	0.0900 (lbs/each)
Product Category	Halogen Reflector Ar, BR, JDR,

Features

average life	2000
Base	GU5.3 Bipin
beam angle	36
dimnable	Yes
lumens	250
Shape	MR16
start type	Instant
Voltage	12.00 V
Voltage Rating	12
Wattage	20

Material, Color, and Finish

color rendering index (cri)	100
color temperature	3000
Finish	Covered

Descriptions

Description	20W MR16 LAMP
extra long description	SYL 20MR16FL35CBAB-12V/54306 20MR16
Long Description	Tungsten Halogen Tru Aim MR16 STANDARD Axial Filament UV Filter Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 20Watt 12Volt Flood Beam
Product Type	20MR16FL35CBAB 12V 20/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135543067
Manufacturers Part Number	20MR16/FL35/C(BAB)-12V/54306
UPC	046135543067

Taxonomies, Classifications, and Categories

Category Description	INCANDESCENT
Type	HALOGEN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	20
Weight Per each	0.09

Uses, Certifications, and Standards

Application	Medium Screwbase or bi-pin
standard	BAB