



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



20T612DCF120 20W 120V T6.5 Double Contact Bayonet Incan Lamp

Ge By Current Lamps

| | |
|------------------|--|
| Catalog Number | 20T612DCF120 |
| Manufacturer | Ge By Current Lamps |
| Description | Ge, 20 WTT, 120 V, 90 LM, 0.813 In Diameter, 5.56 In Length, Double Contact Bayonet (BA15D) Base, 5000 HR Average Life |
| Weight per unit | 0.0600 (lbs/each) |
| Product Category | Incandescent Tubular T Shape L |

Features

| | |
|----------------|--------------------------------|
| average life | 5000.0 |
| Base | Double Contact Bayonet (BA15d) |
| lumens | 90.0 |
| Voltage Rating | 120.0 |
| Wattage | 20.0 |

Material, Color, and Finish

| | |
|--------|-------|
| Color | FROST |
| Finish | Frost |

Dimensions and Weight

| | |
|----------|-------|
| Diameter | 0.813 |
| Length | 5.56 |

Descriptions

| | |
|------------------------|--|
| Description | 20W 120V T6.5 DOUBLE CONTACT BAYONET INCAN LAMP |
| extra long description | GEL 20T61/2DC/F 34241 INCANDESCENT |
| Long Description | GE, 20 WTT, 120 V, 90 LM, 0.813 IN Diameter, 5.56 IN Length, Double Contact Bayonet (BA15d) Base, 5000 HR Average Life |
| Product Type | 34241 Incandescent Lamps |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | GE Current |
| GTIN | 00043168342414 |
| Manufacturers Part Number | 20T61/2DC/F |
| UPC | 043168342414 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | INCANDESCENT |
|----------------------|--------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 60 |
| Weight Per each | 0.06 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application STANDARD