

UPGRADE.
OUTWORK. OUTLAST.

UP TO
3X
MORE
RUN-TIME

UP TO
20%
MORE
POWER

OVER
2X
MORE
LIFE

Milwaukee

M12

REDLITHIUM CP3.0

Milwaukee

M12

REDLITHIUM XC6.0

REDLITHIUM™
CP3.0/XC6.0

M12 REDLITHIUM™ BATTERIES GUIDE

LIGHT DEMAND

FITS M12 TOOLS

HEAVY DEMAND

CP

Less weight
and smaller size

More power
and run-time

XC

More power
and run-time

More power
and run-time

48-11-2430

M12™ REDLITHIUM™
CP3.0 Battery Pack

48-11-2420

M12™ REDLITHIUM™
CP2.0 Battery Pack

48-11-2401

M12™ REDLITHIUM™
CP1.5 Battery Pack

48-11-2460

M12™ REDLITHIUM™
XC6.0 Battery Pack

48-11-2440

M12™ REDLITHIUM™
XC4.0 Battery Pack

48-11-2402

M12™ REDLITHIUM™
XC3.0 Battery Pack

48-11-2411

2-Pack

48-11-2412

2-Pack

USB Rechargeable
700L Focusing Flashlight Kit

2110-21

Lumens	700 / 100 / 700
Modes	High, Low, Strobe
Beam Focus	Slide, Spot/Flood
Water & Dust Rating	IP67
Height	6.5"
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord

REDLITHIUM™ USB
Battery Pack

48-11-2130

Specifications:	
Amp Hours	2.4
Cell Chemistry	LITHIUM-ION
Voltage	4V

USB Rechargeable
Hard Hat Headlamp Kit

2111-21

Lumens	475 / 300 / 300 / 150 / 25
Modes	Spot/Flood, Spot – High, Flood – High/Medium/Low
Water & Dust Rating	IP54
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord, Hard Hat Clips

REDLITHIUM™ USB
Charger

48-59-2002

Specifications:	
Cell Chemistry	LITHIUM-ION
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes

Includes: REDLITHIUM™ USB Charger, 2 ft Heavy Duty USB Cord

REDLITHIUM™ USB
Battery & Charger

48-59-2003

Includes: (1) REDLITHIUM™ USB Battery Pack, REDLITHIUM™ USB Charger, AC Wall Block

USB Rechargeable ROVER™
Magnetic Flood Light Kit

2112-21

Lumens	445 / 100
Modes	High, Low
Hands-Free	Dual Magnets
Water & Dust Rating	IP54
Height	6.0"
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord

MILWAUKEE® Penlight

2105

Lumens	100
Water & Dust Rating	IP67
Height	5.4"
Powered By	(2) AAA

USB Rechargeable
Pivoting Flashlight Kit

2113-21

Lumens	500 / 400 / 100
Modes	Spot – High, Flood – High, Flood – Low
Pivoting Head	110°
Water & Dust Rating	IP54
Height	6.3"
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord

MILWAUKEE® Headlamp

2106

Lumens	300 / 150 / 25
Modes	High, Medium, Low
Water & Dust Rating	IP54
Powered By	(3) AAA

USB Rechargeable ROVER™
Pivoting Flood Light Kit

2114-21

Lumens	550 / 250 / 100
Modes	High, Medium, Low
Pivoting Head	210°
Water & Dust Rating	IP54
Height	4.4"
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord

325L Focusing Flashlight

2107

Lumens	325 / 25
Modes	High, Low
Beam Focus	Slide, Spot/Flood
Water & Dust Rating	IP67
Height	5.0"
Powered By	(3) AAA

2107S: Also Includes Holster

Magnetic Flood Light

2108

Lumens	300 / 100
Modes	High, Low
Water & Dust Rating	IP54
Height	4.8"
Powered By	(2) AA

27

28



RED LITHIUM
USB

Specifications:	
Amp Hours	2.4
Cell Chemistry	LITHIUM-ION
Voltage	4V

A red Milwaukee Red Lithium USB battery and its charging cable. The battery is cylindrical with a black top and bottom. The Milwaukee logo is printed vertically on the side. The charging cable is black with a red USB connector. Below the battery and cable, the text "RED LITHIUM" is written in red, and "USB" is written in white below it.



REDLITHIUM[®]
USB

Cell Chemistry	LITHIUM-ION
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



The image shows the Red Lithium USB logo, which consists of the words "REDLITHIUM" in red and "USB" in white on a black background. Below the logo is a photograph of the product components: a red cylindrical battery, a black USB cable with a red connector, and a black USB adapter.



2105	
Lumens	100
Water & Dust Rating	IP67
Height	5.4"
Powered By	(2) AAA



REDLITHIUM™
USB



2108	
Lumens	300 / 100
Modes	High, Low
Water & Dust Rating	IP54
Height	4.8"
Powered By	(2) AA