



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2107 120/277V 2000W SPST Conduit Mount Die Cast Zinc

*Nsi Industries*

Catalog Number	2107
Manufacturer	Nsi Industries
Description	Conduit Mount, 208 to 277 V, 2000 W, 2 In Width, 3-3/4 In Height, Die Cast Zinc Housing Material, SPST Switch Type, Cadmium Coated CDS Photocell Sensor, -40 °F Operating Temperature, +140 °F Operating Temperature, Conduit Mount, 0.6 LB/Ea
Weight per unit	0.6000 (lbs/each)
Product Category	Lighting Photocells

### Features

supply voltage	120-277 VAC
Timing Range	2 Minutes

### Dimensions and Weight

Size	.500 Conduit Mount
------	--------------------

### Descriptions

Description	120/277V 2000W SPST CONDUIT MOUNT DIE CAST ZINC
extra long description	TORK 2107 Photocontrol Stem Zinc 27

### Manufacturer Information

GTIN	00786261600318
UPC	786261600318

### Taxonomies, Classifications, and Categories

Type	Die Cast Zinc Photocontrol
------	----------------------------

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Weight Per each	0.6

### Uses, Certifications, and Standards

Application	Parking Lot-Building Perimeter-Outdoor Signage Lighting
Enclosure	Zinc Diecast
environmental conditions	-40 to + 140 F
Frequency Rating	50-60 Hz
Mounting	Conduit Mount
Operating Temperature	-40 to + 140 F
standard	UL-CSA