ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



212ELL90 2-1/2" SCH40 90D PVC Elbow

Cantex, Inc

Catalog Number	212ELL90
Manufacturer	Cantex, Inc
Description	Cantex 5133829 Is A 2-1/2 In. X 90-Degree Plain End Schedule 40 Standard Radius Elbow Used to Change The Direction Of A Conduit Run By 90-Degree
Weight per unit	2.3 (lbs/each)
Product Category	PVC SCH 40 Elbows

Dimensions and Weight

Size	2-1/2 in. x 90-Degree Plain End Schedule 40 Standard Radius Elbow

Descriptions

Also Known As...	Elbow Pre-Fab Sweep
Description	2-1/2" SCH40 90D PVC ELBOW
extra long description	CTX 5133829 2 1/2 UL40 90 BND STD R
Features	CANTEX 5133829 is a 2-1/2 in. x 90-Degree Plain End Schedule 40 Standard Radius Elbow used to change the direction of a conduit run by 90-Degree
Long Description	CANTEX 5133829 is a 2-1/2 in. x 90-Degree Plain End Schedule 40 Standard Radius Elbow used to change the direction of a conduit run by 90-Degree
Product Type	2 1/2 UL40 90 BND STD R

Manufacturer Information

Brand	PVC & Accessories
GTIN	00088700568198
Manufacturers Part Number	5133829
UPC	088700153592

Taxonomies, Classifications, and Categories

Category Description	PVC ELBOWS
Type	2-1/2 in. x 90-Degree Plain End Schedule 40 Standard Radius Elbow

Trade Size

Trade Size	2 1/2

Packaging

Carton	1
Package	18
Weight Per each	2.2999