

Products

- > [Index](#)
- > [Featured Products](#)
- > [Cross Reference](#)
- > [UPC Search](#)

Product Datasheet

[Catalog Home](#) [Home Page](#)

[Search](#)

2152 -- EMT/Rigid/IMC Set Screw Coupling 3" Trade Size - Steel



Product Specifications

Family	Rigid and IMC Fittings & EMT Fittings
Fittings Classification	Steel - Set Screw Couplings
Trade Size	3"
Standard Packaging	Carton
Ship Carton Length	4.875
Ship Carton Width	4.875
Ship Carton Height	4.3125
WT. PER HU.	186.6
Unit Carton Quantity	1
Ship Carton Quantity	1
UPC Number	050169021521
Product UPC-A Labeled	Yes
Catalog PDF Page	PDF Catalog Page

Applications

- For use in dry locations to couple two ends of EMT conduit
- RACO® steel set screw couplings provide concrete-tight connections when taped
- RACO® set screw couplings are suitable for applications above 600V

Product Features

- All steel construction insures mechanical protection for the raceway

- Tri-head screws (1/2" to 2" trade sizes) may be installed using a slotted, Philips, or Robertson head screwdriver
- 2-1/2" to 4" trade sizes are also UL listed for use on Rigid/IMC conduit, allowing for design and installation flexibility
- All components are zinc electroplated for corrosion protection

Compliances

C / UL / US

[Login](#) | [Privacy](#) | [Site Map](#)